


# Basler L300 Series

Line Scan Cameras




- Tri-linear CCD color cameras with 2k and 4k resolution
- Excellent color fidelity
- Very cost-effective color line scan cameras

## Color Line Scan with a Compact Housing for Easy Integration

The L300 series highlights Basler's commitment to common sense camera design. These tri-linear cameras offer users a cost-effective way of implementing color in line scan applications. The mono versions with their three monochrome lines can be easily used as a high sensitivity line scan camera. With 3 lines x 2098 pixels per line, L301 series cameras offer an exceptional price/performance ratio. L304 series cameras offer useful new features and high resolution with 3 lines x 4080 pixels per line.

With a choice of three different integration modes as well as adjustable gain and offset, these are very flexible cameras. L300 cameras can be triggered via an external sync signal or operated in an internally controlled „free-run“ mode. All settings can be adjusted by means of simple programming commands via a serial port. The cameras operate with a single voltage power supply and have simple cabling requirements.


Basler L300 cameras are ideal for a variety of applications including document scanning, print inspection, web inspection, food and forestry products inspection, tissue sample scanning, 3-D imaging and measurements, and many other vision applications.



Principle of the Tri-Linear Color Line Scan Camera

### Your benefits include:

- An expensive matched lens is not required to capture optimum image quality, providing you with an affordable solution for color imaging
- Use of a tri-linear sensor results in a very compact camera, reducing the space needed in your installation
- LED indicators and test image generation capability reduce your integration time and aid troubleshooting
- Extensive and complete factory testing ensures consistent product quality
- An integrated spatial correction feature combines pixel data and the lines in the sensor, eliminating the need for computer resources to perform this task
- Electronic exposure time control provides maximum flexibility
- Simple integration into your application is ensured with a combination of new useful features and a Windows® setup tool



## Specifications




Basler L300 Series	L301k	L301kc	L304k	L304kc
Camera Section				
Resolution	3 lines x 2098 pixels		3 lines x 4080 pixels	
Sensor Type	Tri-linear CCD monochrome	Tri-linear CCD color	Tri-linear CCD monochrome	Tri-linear CCD color
Pixel Size	14.0 µm x 14.0 µm x 14.0 µm pitch		10.0 µm x 10.0 µm x 10.0 µm pitch	
Center-to-center-spacing	112 µm		90 µm	
Pixel Clock	20 MHz (in 8 bit triple output mode) 40 MHz (in dual 8 bit or 10 bit output mode) 60 MHz (in single 8 bit or 10 bit output mode)	20 MHz (in 8 bit RGB output mode)	30 MHz (in 8 bit triple output mode), 60 MHz (in dual 8 bit or 10 bit output mode)	30 MHz (in 8 bit RGB output mode), 60 MHz (in dual 8 bit or 10 bit output mode)
Max. Line Rate	9.20 kHz (spatial correction off), 8.0 kHz (spatial correction on)		7.2 kHz	
Video Output Format	Single pixel 8 bits, single pixel 10 bits, dual pixel 8 bits, or 8 bit RGB (selectable)		Dual pixel 8 bits or 10 bits, or 8 bit RGB (selectable)	
Interface	Camera Link (base)			
Synchronization	Via external trigger or free-run			
Exposure Control	Edge-controlled, level-controlled or programmable			
Mechanical/Electrical				
Housing Size (L x W x H)	38.1 mm x 62 mm x 62 mm		41.3 mm x 71 mm x 71 mm	
Housing Temperature	Up to 50°C			
Lens Mount	F-mount		F-mount, M58 x 0.75	
Power Requirements	12VDC (±10%), max. 5.1 W		12VDC (±10%), max. 8.0 W	
Weight (typical)	Max. 282 g		Max. 300 g	
Conformity	CE, FCC			

Specifications may change without prior notice


For detailed technical information, please see the camera manual that can be found on our website: [www.baslerweb.com/manuals](http://www.baslerweb.com/manuals)

## Dimensions (in mm)

L304k/kc



L301k/kc



## Camera Link® Interface

Camera Link is a communication link for visual applications in the fields of science and industry. Camera Link was founded in the year 2000 by Basler and other leading companies in the machine vision arena. Camera Link enables a maximum data transmission rate of 800 MB per second depending on the configuration. Frame grabbers which collect and evaluate the data are usually used to connect the camera and the PC via the Camera Link interface.

The most important benefits afforded by Camera Link are:

- Accepted communication standard for vision technologies (camera frame grabber)
- Simple and standardized cable concept
- Particular suitability for high data rates
- Standardized data protocol for several types of data transfer, for example single/dual tap, 8 bit, 10 bit, RGB, etc.
- Serial communication to the camera via the frame grabber communication port

The standard CameraLink interface used on the L300 family makes these cameras compatible with frame grabbers produced by many different vendors. These vendors include: Cognex, Matrox, National Instruments, Euresys, Matrix Vision, BitFlow, and Mikrotron. An overview showing more frame grabber vendors and frame grabbers compatible with L300 series cameras can be found on the Basler webpage at [www.baslerweb.com](http://www.baslerweb.com).

## What Makes Basler Camera Quality So Special?



To ensure consistently high product quality, we employ several quality inspection procedures during manufacturing. This list describes some of the most essential actions we take to meet your highest requirements.

- The back focal length on each camera is carefully measured and adjusted. This guarantees an optimum distance between the lens flange and the sensor and ensures compliance with optics standards.
- Our advanced Camera Test Tool (CTT+), the first fully-automated inspection system for digital cameras, checks all of the significant quality aspects of each camera we produce. The CTT+ is a unique combination of optics, hardware, and software that can be quickly and efficiently used to calibrate a camera and to measure its performance against a set of standards. For defined sets of conditions, an automated software program examines the camera's output, makes any calibration adjustments necessary, and compares the output to a strictly defined set of performance criteria.



**Basler AG**  
**Germany, Headquarters**  
 Phone +49 4102 463 500  
 Fax +49 4102 463 599  
[bc.sales.europe@baslerweb.com](mailto:bc.sales.europe@baslerweb.com)

**USA**  
 Phone +1 610 280 0171  
 Fax +1 610 280 7608  
[bc.sales.usa@baslerweb.com](mailto:bc.sales.usa@baslerweb.com)

**Singapore**  
 Phone +65 6425 0472  
 Fax +65 6425 0473  
[bc.sales.asia@baslerweb.com](mailto:bc.sales.asia@baslerweb.com)

**Korea**  
 Phone +82 707 1363 114  
 Fax +82 707 0162 705  
[bc.sales.korea@baslerweb.com](mailto:bc.sales.korea@baslerweb.com)

[www.baslerweb.com](http://www.baslerweb.com)